


NIPPLE DRINKING SYSTEM

Quick & easy Assembly



Patent

**PROFESSIONAL POULTRY RAISING
EQUIPMENT MANUFACTURER**

Nipple drinking line



High Quality Low Maintenance

- Square water supply pipe(22mmx22mm)
- Light resistant water pipe prevent algae.
- Nipple with stainless steel body and plastic shell
- Galvanized support pipe.
- Easy push together assembly.
- Folding hangers hold the water pipe firmly in place




nipple drinking system

nipple drinking system consists of nipples,water pipe,presure regulator,front part of drinking line and main water supply pipes.Huabo nipples could give 360°side action triggering.Nipples can offer precision movements of triggering pin getting day-old birds off to the best start.After several years use in the market,the ideal Huabo nipple drinking system ensures that the quality of water being delivered is beneficial and makes drinking easy for birds.


Quick & easy Assembly



End kit with clear sight tube
 Flexible sight tube allows easy pressure reading.
 Strong design



Regulator with clear sight tube
 Deliver different volume of water at an adjustable pressure.
 Heavy construction.
 Pressure regulator with one outlet and with two outlets.



High quality water pipe
 Size:22mmx22mm
 Thickness:2.2mm
 Material:high quality PVC
 Light resistant water pipe prevent algae.

nipple



HB120 nipple

80-120ml/min
 8-12birds/nipple
 Broiler and duck
 15 years



HB80 nipple

50-80ml/min
 8-12birds/nipple
 Breeder and layer
 15 years




SS nipple

Stainless steel shell and body
 Rabbit and duck
 15 years



The easy to install drink cup is available as an option on our watering system.

Front part of drinking line



Quality of the water is of high importance to most drinking system. Special design of our front part not only can supply water and dosatron medicator, but also wash sediment effectively with its large diameter clean-tube. All these can protect the system and reduce the workload.

Medicator



It can dose the water solubility medicine automatically to prevent disease.


By using water pressure as power source instead of electricity, it is economical and reliable.

It can regulate precisely the amount of additive and water ratio.

Easy and convenient operation, anti-rust and anti-corrosion.

Technical data

Flow rate	10L/H-2.5m ³ /H
Working pressure	0.3bar-6bar
Dosing rate	0.02L/H-50L/H
Maximum working temperature	40 °C
Adjustment ratio	0.2% to 2% (1:500-1:50)
Connecting size	external thread G3/4
Water flow	0.45L every other "kata" click sound



Instalaciones de Alta Tecnología
www.sumainternacional.com

Guadalajara:
 Volcán Paricutín 6522,
 Guadalajara, 45070, Jal
 Tel. 52(33)3627-4585

Mérida:
 Calle 80 533,
 Col. Dzununcan
 Mérida, 97315, Yuc.
 Tel. 52(999) 252-9473

Hermosillo:
 Cda. De la Plata 117
 Col. Valle Bonito
 Hermosillo, 82246, Son
 Tel. 52(662) 311-5343

ventas@sumainternacional.com